



AR-206-12-03 (22.5" US std valve)
AR-207-12-03 (22.5" US full)

Instructions for use-

- 1- print PDF at "actual scale" 100% on A4 landscape
- 2- pattern is easier to use if glued to thin cardboard
- 3- use scissors to cut out pattern
- 4- hold pattern inside wheel to check compatibility
- 5- Check clearance of valve (optional dashed cutout) if invisivalves are not to be used
- 6- order best fitting foam heads with stated part number (eg AR-20X-12-03)

Alcoa	22.5x8.25 pcd 285 US
Accuride	22.5x8.25 pcd 285 US
Forge	22.5x8.25 pcd 285 US
SSA	22.5x8.25 pcd 285 US

Note- this pattern can be up to 5mm out as foam heads and polishing fleece is designed to mould to different profiles

DESCRIPTION	SHEET 1-1
DATE	PROJECT
Aussie Rimshine	

